

ADM FRANKFURT

Diamond Metallic Abrasive (ADM)
destined to calibrate and grind.

TECHNOLOGIES: ▼





_A controlled and homogeneous dispersion of the diamond, make this technology the perfect combination to achieve superior **Diamond Metallic Abrasives**.





_ **Specific formulations** developed to optimize the polishing of different materials.

_ **Undefined storage keeping** stable without changing its properties over time.





_ **Increase in the productivity** with respect to the traditional abrasive, avoiding the continuous machine stops.



PERFORMANCE
■ ADR abrasive
■ Traditional abrasive

MATERIALS ▼	MACHINES ▼
<ul style="list-style-type: none"> ✓ MARBLE / MR ✓ TERRAZZO / TR ✓ GRANITE / GR ✓ CONCRETE / CON 	<div style="display: flex; flex-wrap: wrap; justify-content: space-around;"> <div style="text-align: center;">  AUTOMATIC </div> <div style="text-align: center;">  SEMI-AUTOMATIC </div> <div style="text-align: center;">  CNC </div> <div style="text-align: center;">  PLANETARY </div> </div>

AVAILABLE OPTIONS: ▼

GRITS ▶	10-20-40-60-80-100-120-140-170-200
HARDNESS ▶	MR - GR - CON
OPTIONS ▶	<div style="display: flex; align-items: center;">   </div> <p>NORMAL RESIN[®]</p>
AVAILABILITY ▶	<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> 4 TABLETS</div> <div style="text-align: center;"> 6 TABLETS</div> <div style="text-align: center;"> 8 TABLETS</div> </div>
DISPOSITION ▶	<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> LINE</div> <div style="text-align: center;"> SPYKE</div> <div style="text-align: center;"> LEGO</div> </div>
UNITS ▶	<div style="display: flex; align-items: center;">  <div style="margin-left: 20px; border: 1px solid gray; padding: 2px;">ref. 010101</div> </div>



MORE INFORMATION ▼

VISIT our channel

AbrasiveAlicante

ANY DOUBT?
 CALL US
 (+34) 965 112 713




_Example of maximum industrial automation by means of a multi-press system executed by robotic arms. Hereby we ensure the **maximum precision in processes and products**, with **constant quality** that differentiates us.



_All ADM Frankfurt can be **resin coated**. This allows to apply greater pressure on the tools in the process, achieving a **greater texture**.

_Recommended option when treating very hard stones.




_ **100% effective** structured abrasives 100% from the beginning. The **linear micro-structure** defined in the upper part of the BIT, allows a perfect job from the beginning, no need to prepare or open the tool previously.

_ Lightened metallic base **reducing by half** the weight of the tool.

_ **Minimizes breakdowns and maintenance** of the heads.



_ **Universal coupling** type Frankfurt, with **quick change**, adaptable to all the machines of the market.



_ This product does not contain substances prohibited according to the regulation (CE) n°1907 / 2006



ISO 9001:2015 CERTIFICATED
 www.abrasivosalicante.com

