



160MM FICKERT ADR

Diamond Resined Abrasive (ADR),
destined to polish and gloss.

MATERIALS ▼

- ✓ QUARTZ / QZ
- ✓ CERAMIC / CR

MACHINES ▼



AUTOMATIC



SEMI-AUTOMATIC



CNC

AVAILABLE OPTIONS: ▼

GRITS ▶ 36-46-60-80-100-120-150-180-220-240-280-320-400-600-800-1000-1200-1500-1800-2000-3000-4000-5000-6000-Lux

HARDNESS ▶ QZ - CR - GR



NORMAL



FORCE SYSTEM®

OPTIONS ▶

UNITS ▶ 1

ref. 020202

MORE INFORMATION ▼



VISIT our channel
YouTube

AbrasivosAlicante



ANY DOUBT?

CALL US
(+34) 965 112 713



TECHNOLOGIES: ▼





A controlled and homogeneous dispersion of the diamond, make this technology the perfect combination to achieve superior **Diamond Resin Abrasives**.

Specific formulations developed to optimize the polishing of different materials.

Undefined storage keeping stable without changing its properties over time.

Increase in the productivity with respect to the traditional abrasive, avoiding the continuous machine stops.



RENDIMIENTO
■ Abrasivo ADR
■ Abrasivo tradicional



The construction of the tool combining flexible with rigid parts guarantees a perfect coupling and a constant contact on surfaces, **avoiding marks and scratches on the polish**.

We recommend applying **Force System technology on the finest grains** to achieve the highest polishing and shining quality.



Example of maximum industrial automation by means of a multi-press system executed by robotic arms. Hereby we ensure the **maximum precision in processes and products**, with **constant quality** that differentiates us.



Individual identification by marking with a numerical button, informing of the corresponding grain.



Ecological. This product does not contain substances prohibited according to the regulation (CE) n°1907 / 2006



ISO 9001:2015 CERTIFIED
www.abrasivosalicante.com

ABRASIVOS
ALICANTE