



FICKERT ADR LAP

Diamond Resined Abrasive (ADR), destined to "Lapping" and Semi-Polishing.

MATERIALS ▼

MACHINES ▼

✓ CERAMIC / CR



AUTOMATIC

AVAILABLE OPTIONS: ▼

GRITS ▶ 60-80-100-120-150-180-220-240-280-320-400-600-800-1000-1200-1500-1800-2000-3000-4000-5000-6000

OPTIONS ▶



100mm



140mm

UNITS ▶



ref. 020204

MORE INFORMATION ▼



VISIT our channel

YouTube


AbrasivosAlicante



ANY DOUBT?

CALL US

(+34) 965 112 713



TECNOLOGIES: ▼



ADR®

_A controlled and homogeneous dispersion of the diamond, make this technology the perfect combination to achieve superior **Diamond Resin Abrasives**.

_ **Specific formulations** developed to optimize the polishing of different materials.

_ **Undefined storage keeping** stable without changing its properties over time.

_ **Increase in the productivity** with respect to the traditional abrasive, avoiding the continuous machine stops.




PERFORMANCE
ADR abrasive
Traditional abrasive

FORCE SYSTEM®

_The construction of the tool combining flexible with rigid parts guarantees a perfect coupling and a constant contact on surfaces, **avoiding marks and scratches on the polish**.

_We recommend applying **Force System technology on the finest grains** to achieve the highest polishing and shining quality.




ROBOT MULTI-PRESS

_Example of maximum industrial automation by means of a multi-press system executed by robotic arms. Hereby we ensure the **maximum precision in processes and products**, with **constant quality** that differentiates us.



_ **Individual identification** by marking with a numerical button, informing of the corresponding grain.



_ **Ecological**. This product does not contain substances prohibited according to the regulation (CE) n°1907 / 2006



ISO 9001:2015 CERTIFICATED
www.abrasivosalicante.com

ABRASIVOS
ALICANTE